
2SK3163 Spice parameter

```
.SUBCKT 2sk3163 1 2 3
* Model generated on Jul 26, 99
* MODEL FORMAT: SPICE3
* Symmetry POWER MOS Model (Version 1.0)
* External Node Designations
* Node 1 -> Drain
* Node 2 -> Gate
* Node 3 -> Source
M1 9 7 8 8 MM L=100u W=100u
* Default values used in MM:
* The voltage-dependent capacitances are
* not included. Other default values are:
* RS=0 RD=0 LD=0 CBD=0 CBS=0 CGB0=0
.MODEL MM NMOS LEVEL=1 IS=1e-32
+VTO=2.31758 LAMBDA=0 KP=177.858
+CGS0=7.06858e-05 CGD0=1.17288e-06
RS 8 3 0.00377789
D1 3 1 MD
.MODEL MD D IS=5e-09 RS=0.01 N=1 BV=300
+IBV=10 EG=1.11 XTI=3 TT=0.0001
+CJO=3.55919e-09 VJ=0.5 M=0.534639 FC=0.5
RDS 3 1 1e+06
RD 9 1 0.00402685
RG 2 7 45.6765
D2 4 5 MD1
* Default values used in MD1:
* RS=0 EG=1.11 XTI=3.0 TT=0
* BV=infinite IBV=1mA
.MODEL MD1 D IS=1e-32 N=50
+CJO=1.70059e-10 VJ=16.4094 M=0.9 FC=1.00008e-08
D3 0 5 MD2
* Default values used in MD2:
* EG=1.11 XTI=3.0 TT=0 CJO=0
* BV=infinite IBV=1mA
.MODEL MD2 D IS=1e-10 N=0.4 RS=3e-06
RL 5 10 1
FI2 7 9 VFI2 -1
VFI2 4 0 0
EV16 10 0 9 7 1
CAP 11 10 2.22241e-10
FI1 7 9 VFI1 -1
VFI1 11 6 0
RCAP 6 10 1
D4 0 6 MD3
* Default values used in MD3:
* EG=1.11 XTI=3.0 TT=0 CJO=0
* RS=0 BV=infinite IBV=1mA
.MODEL MD3 D IS=1e-10 N=0.4
.ENDS 2sk3163
```