
HZM27WA Spice parameter

```
* Model generated on Oct 2, 97
* MODEL FORMAT: SPICE3, PSpice apply.
* UCB DIODE Model
.MODEL HZM27WA D
+IS=1.0E-12
+CJO=2.65E-11
+TT=1.0E-9
+BV=27.1
+XTI=3
+RS=89
+M=0.332
+EG=1.11
+IBV=8.5E-8
+KF=0
+N=0.8
+VJ=0.7
+FC=0.5
+AF=1
**** END of HZM27WA (Surge absorption diode)
*      IS: Saturation current, Unit:A
*      CJO: Junction capacitance, Unit:F
*      TT: Transit time, Unit: sec
*      BV: Rev.breakdown voltage, Unit:V
*      XTI: Isat temperature exp.
*      RS: Ohmic resistance, Unit: Ohm
*      M: Grading coefficient
*      EG: Activation energy, Unit:Ve
*      IBV: I at V-breakdown, Unit:A
*      KF: Flicker noise coefficient
*      N: Emission coefficient
*      VJ: Junction potential, Unit:V
*      FC: Depretion cap. Coefficient
*      AF: Flicker noise exp.
```